


Allsheng Nano-100/300/400/400A/500 Mikro Spektrofotometre, Nanodrop Spektrofotometre






■ Adding sample



■ Measuring sample



■ quick and easy cleaning



SPECIFICATION	Nano-300	Nano-400A	Nano-500
Wave Length	Between 200~800nm	Between 260nm ve 280nm	Between 200~800nm arası
Volume	0.5~2.0ul	1~2.0ul	0.5~2.0ul
Light Source	Xenon flash lamp	UV LED	Xenon flash lamp
Dedector	2048 linear CCD array	UV silicon photocell	2048 linear CCD array
Absorbans distance	0.02 - 90A	0.02 - 80A	0.02 - 100A

